



# Selenium

## SGP340 CPO-TW45W K EB II OR PC 48/60

Vital, MASTER CosmoWhite CPO-TW, 45 W, Electronic, Safety class II, Open CT-POT, Polycarbonate bowl/cover, Universal for diameter 48 to 60 mm

Selenium SGP340 is an efficient, ergonomic road-lighting luminaire. Its simple, rounded form reduces its daytime visual impact, allowing it to integrate into any kind of environment. Selenium incorporates the renowned T-POT reflector for excellent optical performance. Energy savings are possible by means of dimming with a switch or stand-alone Chronosense system (without pilot cable). Selenium is suitable for side-entry or post-top mounting, with a choice of three tilt angles for optimal installation (0, 5, 15°).

### Product data


General Information		Optic type outdoor	
Lamp family code	CPO-TW [MASTER CosmoWhite CPO-TW]	Open CT-POT	
Cap-Base	PGZ12 [PGZ12]	Operating and Electrical	
Gear	EB [Electronic]	Input Voltage	220 to 240 V
Photocell	-	Power Consumption	45 W
Product family code	SGP670 [Vital]	Mechanical and Housing	
Embedded control	-	Housing Color	Grey
CE mark	Yes	Mounting device	Universal for diameter 48 to 60 mm
ENEC mark	-	Overall height	268 mm
Light Technical		Approval and Application	
Standard tilt angle posttop	5°	Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Standard tilt angle side entry	0°	Mech. impact protection code	IK10 [20 J vandal-resistant]
Number of light sources	1		
Optical cover type	Polycarbonate bowl/cover		

# Selenium

Protection class IEC	Safety class II
<b>Product Data</b>	
Order product name	SGP340 CPO-TW45W K EB II OR PC 48/60
Full product name	SGP340 CPO-TW45W K EB II OR PC 48/60
Full product code	872790062615500
Order code	62615500

Material Nr. (12NC)	910500967012
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900626155
Numerator - Packs per outer box	1
EAN/UPC - Case	8727900626155

## Dimensional drawing



### Product

SGP340 CPO-TW45W K EB II OR PC 48/60

