



Selenium

SGP340 CPO-TW60W K EBR II OR FG LS-8 48/

Vital, MASTER CosmoWhite CPO-TW, 60 W, Electronic regulating, Safety class II, Open CT-POT, Flat glass, LumiStep dimming 8 hours, Universal for diameter 48 to 60 mm

Selenium SGP340 is an efficient, ergonomic road-lighting luminaire. Its simple, rounded form reduces its daytime visual impact, allowing it to integrate into any kind of environment. Selenium incorporates the renowned T-POT reflector for excellent optical performance. Energy savings are possible by means of dimming with a switch or stand-alone Chronosense system (without pilot cable). Selenium is suitable for side-entry or post-top mounting, with a choice of three tilt angles for optimal installation (0, 5, 15°).


Product data

General Information		Optic type outdoor	
Lamp family code	CPO-TW [MASTER CosmoWhite CPO-TW]	Open CT-POT	
Cap-Base	PGZ12 [PGZ12]	Operating and Electrical	
Gear	EBR [Electronic regulating]	Input Voltage	220 to 240 V
Photocell	-	Power Consumption	60 W
Product family code	SGP670 [Vital]	Mechanical and Housing	
CE mark	Yes	Housing Color	Grey
ENEC mark	-	Mounting device	Universal for diameter 48 to 60 mm
Embedded control	LumiStep dimming 8 hours	Overall height	232 mm
Light Technical		Approval and Application	
Standard tilt angle posttop	5°	Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Standard tilt angle side entry	0°	Mech. impact protection code	IK08 [5 J vandal-protected]
Number of light sources	1		
Optical cover type	Flat glass		

Protection class IEC	Safety class II
Product Data	
Order product name	SGP340 CPO-TW60W K EBR II OR FG LS-8 48/
Full product name	SGP340 CPO-TW60W K EBR II OR FG LS-8 48/
Full product code	872790062624700
Order code	910500967912

Material Nr. (12NC)	910500967912
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900626247
Numerator - Packs per outer box	1
EAN/UPC - Case	8727900626247

Dimensional drawing



Product
SGP340 CPO-TW60W K EBR II OR FG LS-8 48/

