



Urbana

EPS300 PL-T/4P42W HFP 220-240V HSH

URBANA, MASTER PL-T 4 Pin, 42 W, HF Performer

Comprising eight different decorative models, the Urbana EPS300 range can be deployed in a wide variety of urban applications. At the same time, a distinct family design aesthetic is maintained thanks to the use of a single standard pole mount across the entire range. Whatever the application, Urbana's combination of excellent lighting performance and attractive day-time and night-time appearance adds to the ambience of the surroundings. The luminaires with Forest, Arctic and Tropic top covers address the issue of obtrusive light by means of dedicated bowls with top covers that prevent upward emission of light. The light pollution bowl Luner features a black coating on its upper hemisphere, to prevent upward light distribution. Both the opal Polar and clear Cristal bowls offer a choice of soft, diffuse lighting and bright, direct illumination.

Product data

General Information		Mech. impact protection code		IK10 [20 J vandal-resistant]
Lamp family code	PL-T/4P [MASTER PL-T 4 Pin]	Protection class IEC		Safety class II
Cap-Base	GX24Q-4 [GX24q-4]	Product Data		
Gear	HFP [HF Performer]	Order product name	EPS300 PL-T/4P42W HFP 220-240V HSH	
Product family code	EPS300 [URBANA]	Full product name	EPS300 PL-T/4P42W HFP 220-240V HSH	
CE mark	Yes	Full product code	871155912623400	
ENEC mark	-	Order code	12623400	
Operating and Electrical		Material Nr. (12NC)	910500971212	
Input Voltage	220/240 V	Numerator - Quantity Per Pack	1	
Power Consumption	42 W	EAN/UPC - Product/Case	8711559126234	
Approval and Application		Numerator - Packs per outer box	1	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]	EAN/UPC - Case	8711559126234	

Dimensional drawing

