



Urbana

EPS300 CDO-ET100W IC HSH

URBANA, MASTER CityWhite CDO-ET, 100 W

Comprising eight different decorative models, the Urbana EPS300 range can be deployed in a wide variety of urban applications. At the same time, a distinct family design aesthetic is maintained thanks to the use of a single standard pole mount across the entire range. Whatever the application, Urbana's combination of excellent lighting performance and attractive day-time and night-time appearance adds to the ambience of the surroundings. The luminaires with Forest, Arctic and Tropic top covers address the issue of obtrusive light by means of dedicated bowls with top covers that prevent upward emission of light. The light pollution bowl Luner features a black coating on its upper hemisphere, to prevent upward light distribution. Both the opal Polar and clear Cristal bowls offer a choice of soft, diffuse lighting and bright, direct illumination.

Product data

General Information	
Lamp family code	CDO-ET [MASTER CityWhite CDO-ET]
Cap-Base	E40 [E40]
Gear	CONV [Conventional]
Product family code	EPS300 [URBANA]
CE mark	Yes
ENEC mark	ENEC mark
Operating and Electrical	
Input Voltage	230 V (default) or 240 V
Power Consumption	100 W
Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]

Mech. impact protection code	IK10 [20 J vandal-resistant]
Protection class IEC	Safety class II
Product Data	
Order product name	EPS300 CDO-ET100W IC HSH
Full product name	EPS300 CDO-ET100W IC HSH
Full product code	872790062545500
Order code	62545500
Material Nr. (12NC)	910500978612
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900625455
Numerator - Packs per outer box	1
EAN/UPC - Case	8727900625455

Dimensional drawing

