



Urbana

EPS300 CDO-TT70W IC HSH

URBANA, MASTER CityWhite CDO-TT, 70 W

Comprising eight different decorative models, the Urbana EPS300 range can be deployed in a wide variety of urban applications. At the same time, a distinct family design aesthetic is maintained thanks to the use of a single standard pole mount across the entire range. Whatever the application, Urbana's combination of excellent lighting performance and attractive day-time and night-time appearance adds to the ambience of the surroundings. The luminaires with Forest, Arctic and Tropic top covers address the issue of obtrusive light by means of dedicated bowls with top covers that prevent upward emission of light. The light pollution bowl Luner features a black coating on its upper hemisphere, to prevent upward light distribution. Both the opal Polar and clear Cristal bowls offer a choice of soft, diffuse lighting and bright, direct illumination.

Product data

General Information		Mech. impact protection code	
Lamp family code	CDO-TT [MASTER CityWhite CDO-TT]	Mech. impact protection code	IK10 [20 J vandal-resistant]
Cap-Base	E27 [E27]	Protection class IEC	Safety class II
Gear	CONV [Conventional]	Product Data	
Product family code	EPS300 [URBANA]	Order product name	EPS300 CDO-TT70W IC HSH
CE mark	Yes	Full product name	EPS300 CDO-TT70W IC HSH
ENEC mark	ENEC mark	Full product code	872790062542400
Operating and Electrical		Order code	62542400
Input Voltage	230 V (default) or 240 V	Material Nr. (12NC)	910500982412
Power Consumption	70 W	Numerator - Quantity Per Pack	1
Approval and Application		EAN/UPC - Product/Case	8727900625424
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]	Numerator - Packs per outer box	1
		EAN/UPC - Case	8727900625424

Dimensional drawing

