



Urbana

EPS300 SON-T50W IC HSH

URBANA, SON-T, 50 W

Comprising eight different decorative models, the Urbana EPS300 range can be deployed in a wide variety of urban applications. At the same time, a distinct family design aesthetic is maintained thanks to the use of a single standard pole mount across the entire range. Whatever the application, Urbana's combination of excellent lighting performance and attractive day-time and night-time appearance adds to the ambience of the surroundings. The luminaires with Forest, Arctic and Tropic top covers address the issue of obtrusive light by means of dedicated bowls with top covers that prevent upward emission of light. The light pollution bowl Luner features a black coating on its upper hemisphere, to prevent upward light distribution. Both the opal Polar and clear Cristal bowls offer a choice of soft, diffuse lighting and bright, direct illumination.

Product data

General Information		Mech. impact protection code	
Lamp family code	SON-T [SON-T]	IK10 [20 J vandal-resistant]	
Cap-Base	E27 [E27]	Protection class IEC	
Gear	CONV [Conventional]	Safety class II	
Product family code	EPS300 [URBANA]	Product Data	
CE mark	Yes	Order product name	EPS300 SON-T50W IC HSH
ENEC mark	ENEC mark	Full product name	EPS300 SON-T50W IC HSH
Operating and Electrical		Full product code	872790062585100
Input Voltage	230 V (default) or 240 V	Order code	62585100
Power Consumption	50 W	Material Nr. (12NC)	910500983912
Approval and Application		Numerator - Quantity Per Pack	1
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]	EAN/UPC - Product/Case	8727900625851
		Numerator - Packs per outer box	1
		EAN/UPC - Case	8727900625851

Dimensional drawing

