



Urbana

EPS300 MAX100W-E27 LO-D/I

URBANA

Comprising eight different decorative models, the Urbana EPS300 range can be deployed in a wide variety of urban applications. At the same time, a distinct family design aesthetic is maintained thanks to the use of a single standard pole mount across the entire range. Whatever the application, Urbana's combination of excellent lighting performance and attractive day-time and night-time appearance adds to the ambience of the surroundings. The luminaires with Forest, Arctic and Tropic top covers address the issue of obtrusive light by means of dedicated bowls with top covers that prevent upward emission of light. The light pollution bowl Luner features a black coating on its upper hemisphere, to prevent upward light distribution. Both the opal Polar and clear Cristal bowls offer a choice of soft, diffuse lighting and bright, direct illumination.

Product data

General Information	
Cap-Base	E27 [E27]
Gear	-
Product family code	EPS300 [URBANA]
CE mark	Yes
ENEC mark	-
Operating and Electrical	
Input Voltage	220 to 240 V
Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK10 [20 J vandal-resistant]
Protection class IEC	Safety class II

Product Data	
Order product name	EPS300 MAX100W-E27 LO-D/I
Full product name	EPS300 MAX100W-E27 LO-D/I
Full product code	871829104094100
Order code	04094100
Material Nr. (12NC)	910500990212
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291040941
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291040941

Dimensional drawing

