PHILIPS

Lighting



Iridium SGS252/452

SGS452 SON-T70W I OR GB GR SND

IRIDIUM, SON-T, 70 W, Open CT-POT, Glass bowl/cover

Modular road-lighting luminaire offering a wide choice of optical, electrical and mechanical combinations to make driving safer and more comfortable. Ensures low cost of ownership thanks to its superior optics and low maintenance and installation costs

Product data

General Information	
Lamp family code	SON-T [SON-T]
Gear	CONV [Conventional]
Product family code	SGS452 [IRIDIUM]
CE mark	Yes
ENEC mark	ENEC mark

Light Technical	
Standard tilt angle posttop	5°
Standard tilt angle side entry	5°
Number of light sources	1
Optical cover type	Glass bowl/cover
Optic type outdoor	Open CT-POT

Operating and Electrical	
Input Voltage	230 V
Power Consumption	70 W
Cable	-

Mechanical and Housing	
Housing Color	Grey
Mounting device	-
Overall height	219 mm
Parts color	-


Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Protection class IEC	Safety class I

Product Data	
Order product name	SGS452 SON-T70W I OR GB GR SND
Full product name	SGS452 SON-T70W I OR GB GR SND
Full product code	871155947642100
Order code	47642100
Material Nr. (12NC)	910502109518
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711559476421
Numerator - Packs per outer box	1

Iridium SGS252/452

EAN/UPC - Case	8711559476421

Dimensional drawing



Product	A
SGS452 SON-T70W I OR GB GR SND	219 mm

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.