



Iridium SGS252/452

SGS252 SON-T70W K II OR GB GR SND

IRIDIUM - SON-T - 70 W - Open CT-POT - Glass bowl/cover

Modular road-lighting luminaire offering a wide choice of optical, electrical and mechanical combinations to make driving safer and more comfortable. Ensures low cost of ownership thanks to its superior optics and low maintenance and installation costs

Product data

General Information	
Number of light sources	1 [1 pc]
Lamp family code	SON-T [SON-T]
Lamp power	70 W
Kombipack	Lamp(s) included
Compensation circuit	Capacitive
Gear	CONV [Conventional]
Optical cover/lens type	GB [Glass bowl/cover]
Electrical circuit protection	-
Cable	-
Protection class IEC	Safety class II (II)
Parts color	-
CE mark	CE mark
ENEC mark	ENEC mark
Optic type outdoor	Open CT-POT
Colored frame	-
RAL color	-
Filter coil	-
Product family code	SGS252 [IRIDIUM]


Light Technical	
Standard tilt angle posttop	5°
Standard tilt angle side entry	5°
Operating and Electrical	
Input Voltage	230 V
Ignitor	SND [Digital semi-parallel]
Mechanical and Housing	
Mounting device	60/76 [Spigot for diameter 60-76 mm]
Overall height	219 mm
Color	Gray
Dimensions (Height x Width x Depth)	219 x NaN x NaN mm (8.6 x NaN x NaN in)
Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Product Data	
Full product code	871155984251600

Iridium SGS252/452

Order product name	SGS252 SON-T70W K II OR GB GR SND
EAN/UPC - Product	8711559842516
Order code	84251600
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Material Nr. (12NC)	910502121718
Net Weight (Piece)	8.242 kg

Dimensional drawing



Iridium SGS252

