



Iridium SGS253/453

SGS253 SON-T100W K II CR PC GR SND

IRIDIUM, SON-T, 100 W, Closed CT-POT, Polycarbonate bowl/cover

Modular road-lighting luminaires offering a wide choice of optical, electrical and mechanical combinations to make driving safer and more comfortable. Ensures low cost of ownership thanks to its superior optics and low maintenance and installation costs.


Product data

General Information		Power Consumption	
Lamp family code	SON-T [SON-T]	100 W	
Gear	CONV [Conventional]	Mechanical and Housing	
Photocell	-	Housing Color	Grey
Product family code	SGS253 [IRIDIUM]	Overall height	289 mm
Embedded control	-	Parts color	-
CE mark	Yes	Approval and Application	
ENEC mark	ENEC mark	Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Light Technical		Mech. impact protection code	IK08 [5 J vandal-protected]
Standard tilt angle posttop	5°	Protection class IEC	Safety class II
Standard tilt angle side entry	5°	Product Data	
Number of light sources	1	Order product name	SGS253 SON-T100W K II CR PC GR SND
Optical cover type	Polycarbonate bowl/cover	Full product name	SGS253 SON-T100W K II CR PC GR SND
Optic type outdoor	Closed CT-POT	Full product code	871155984262200
Operating and Electrical		Order code	84262200
Input Voltage	230 V	Material Nr. (12NC)	910502123618
		Numerator - Quantity Per Pack	1

Iridium SGS253/453

EAN/UPC - Product/Case	8711559842622
Numerator - Packs per outer box	1
EAN/UPC - Case	8711559842622

Dimensional drawing



Product	A
SGS253 SON-T100W K II CR PC GR SND	289 mm

