



Iridium SGS252/452

SGS452 CDO-TT70W K II CR FG GR SND

IRIDIUM - MASTER CityWhite CDO-TT - 70 W - Closed CT-POT
- Flat glass

Modular road-lighting luminaire offering a wide choice of optical, electrical and mechanical combinations to make driving safer and more comfortable. Ensures low cost of ownership thanks to its superior optics and low maintenance and installation costs

Product data

General Information	
Number of light sources	1 [1 pc]
Lamp family code	CDO-TT [MASTER CityWhite CDO-TT]
Lamp power	70 W
Kombipack	Lamp(s) included
Compensation circuit	-
Gear	CONV [Conventional]
Optical cover/lens type	FG [Flat glass]
Electrical circuit protection	-
Cable	-
Protection class IEC	Safety class II (II)
Parts color	-
CE mark	CE mark
ENEC mark	ENEC mark
Optic type outdoor	Closed CT-POT
Colored frame	-
RAL color	-
Filter coil	-

Product family code	SGS452 [IRIDIUM]
Light Technical	
Standard tilt angle posttop	5°
Standard tilt angle side entry	5°
Operating and Electrical	
Input Voltage	230 V
Ignitor	SND [Digital semi-parallel]
Mechanical and Housing	
Mounting device	No [-]
Overall height	187 mm
Color	Gray
Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]


Iridium SGS252/452

Product Data

Full product code	871155984329200
Order product name	SGS452 CDO-TT70W K II CR FG GR SND
EAN/UPC - Product	8711559843292
Order code	84329200
Numerator - Quantity Per Pack	1

Numerator - Packs per outer box	1
Material Nr. (12NC)	910502127318
Net Weight (Piece)	9.423 kg

Dimensional drawing



Iridium SGS252

