



Iridium SGS253/453

SGS253 CDO-TT100W K II OR GB GR SND

IRIDIUM, MASTER CityWhite CDO-TT, 100 W, Open CT-POT, Glass bowl/cover

Modular road-lighting luminaires offering a wide choice of optical, electrical and mechanical combinations to make driving safer and more comfortable. Ensures low cost of ownership thanks to its superior optics and low maintenance and installation costs.


Product data

General Information		Power Consumption	
Lamp family code	CDO-TT [MASTER CityWhite CDO-TT]	100 W	
Gear	CONV [Conventional]	Mechanical and Housing	
Photocell	-	Housing Color	Grey
Product family code	SGS253 [IRIDIUM]	Overall height	224 mm
Embedded control	-	Parts color	-
CE mark	Yes	Approval and Application	
ENEC mark	ENEC mark	Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Light Technical		Mech. impact protection code	IK08 [5 J vandal-protected]
Standard tilt angle posttop	5°	Protection class IEC	Safety class II
Standard tilt angle side entry	5°	Product Data	
Number of light sources	1	Order product name	SGS253 CDO-TT100W K II OR GB GR SND
Optical cover type	Glass bowl/cover	Full product name	SGS253 CDO-TT100W K II OR GB GR SND
Optic type outdoor	Open CT-POT	Full product code	871155984478700
Operating and Electrical		Order code	84478700
Input Voltage	230 V	Material Nr. (12NC)	910502136018
		Numerator - Quantity Per Pack	1

Iridium SGS253/453

EAN/UPC - Product/Case	8711559844787
Numerator - Packs per outer box	1
EAN/UPC - Case	8711559844787

Dimensional drawing



Product	A
SGS253 CDO-TT100W K II OR GB GR SND	224 mm

