



# Iridium SGS254/454

## SGS254 SON-T250W K II CP FG GR SND

IRIDIUM, SON-T, 250 W, Closed T-POT, Flat glass

Modular road-lighting luminaire offering a wide choice of optical, electrical and mechanical combinations to make driving safer and more comfortable. Ensures low cost of ownership thanks to its superior optics and low maintenance and installation costs.

### Product data

General Information	
Lamp family code	SON-T [SON-T]
Product family code	SGS254 [IRIDIUM]
CE mark	Yes
Light Technical	
Optical cover type	Flat glass
Optic type outdoor	Closed T-POT
Operating and Electrical	
Power Consumption	250 W
Mechanical and Housing	
Housing Color	Grey

Approval and Application	
Protection class IEC	Safety class II
Product Data	
Order product name	SGS254 SON-T250W K II CP FG GR SND
Full product name	SGS254 SON-T250W K II CP FG GR SND
Full product code	871155984481700
Order code	84481700
Material Nr. (12NC)	910502136318
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711559844817
Numerator - Packs per outer box	1
EAN/UPC - Case	8711559844817

Iridium SGS254/454

Dimensional drawing

