



# Iridium SGS252/452

## SGS452 CDO-TT100W K II OR GB AL 7035 SND

IRIDIUM - MASTER CityWhite CDO-TT - 100 W - Open CT-POT  
 - Glass bowl/cover

Modular road-lighting luminaire offering a wide choice of optical, electrical and mechanical combinations to make driving safer and more comfortable. Ensures low cost of ownership thanks to its superior optics and low maintenance and installation costs

### Product data

General Information	
Number of light sources	1 [ 1 pc]
Lamp family code	CDO-TT [ MASTER CityWhite CDO-TT]
Lamp power	100 W
Kombipack	Lamp(s) included
Compensation circuit	-
Gear	CONV [ Conventional]
Optical cover/lens type	GB [ Glass bowl/cover]
Electrical circuit protection	-
Cable	-
Protection class IEC	Safety class II (II)
Parts color	All parts colored
CE mark	CE mark
ENEC mark	ENEC mark
Optic type outdoor	Open CT-POT
Colored frame	-
RAL color	Light gray (7035)
Filter coil	-


Product family code	SGS452 [ IRIDIUM]
Light Technical	
Standard tilt angle posttop	5°
Standard tilt angle side entry	5°
Operating and Electrical	
Input Voltage	230 V
Ignitor	SND [ Digital semi-parallel]
Mechanical and Housing	
Mounting device	60/76 [ Spigot for diameter 60-76 mm]
Overall height	219 mm
Color	RAL (to be defined)
Dimensions (Height x Width x Depth)	219 x NaN x NaN mm (8.6 x NaN x NaN in)
Approval and Application	
Ingress protection code	IP66 [ Dust penetration-protected, jet-proof]

## Iridium SGS252/452

Mech. impact protection code	IK08 [ 5 J vandal-protected]
<b>Product Data</b>	
Full product code	871155984942300
Order product name	SGS452 CDO-TT100W K II OR GB AL 7035 SND
EAN/UPC - Product	8711559849423
Order code	84942300

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	910502155418
Net Weight (Piece)	9.847 kg

### Dimensional drawing



Iridium SGS252

