



Iridium SGS253/453

SGS253 CDO-TT150W K II CR PC GR SND

IRIDIUM - MASTER CityWhite CDO-TT - 150 W - Closed CT-POT
 - Polycarbonate bowl/cover

Modular road-lighting luminaires offering a wide choice of optical, electrical and mechanical combinations to make driving safer and more comfortable. Ensures low cost of ownership thanks to its superior optics and low maintenance and installation costs.

Product data

General Information	
Number of light sources	1 [1 pc]
Lamp family code	CDO-TT [MASTER CityWhite CDO-TT]
Lamp power	150 W
Kombipack	Lamp(s) included
Gear	CONV [Conventional]
Optical cover/lens type	PC [Polycarbonate bowl/cover]
Embedded control	No [-]
Light regulation	-
Protection class IEC	Safety class II (II)
Parts color	-
CE mark	CE mark
ENEC mark	ENEC mark
Optic type outdoor	Closed CT-POT
Colored frame	-
Filter coil	-
Photocell	No [-]
Product family code	SGS253 [IRIDIUM]


Light Technical	
Standard tilt angle posttop	5°
Standard tilt angle side entry	5°
Operating and Electrical	
Input Voltage	230 V
Ignitor	SND [Digital semi-parallel]
Mechanical and Housing	
Overall height	289 mm
Color	Gray
Dimensions (Height x Width x Depth)	289 x NaN x NaN mm (11.4 x NaN x NaN in)
Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Product Data	
Full product code	871155984943000

Iridium SGS253/453

Order product name	SGS253 CDO-TT150W K II CR PC GR SND
EAN/UPC - Product	8711559849430
Order code	84943000
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1



Material Nr. (12NC)	910502155518
Net Weight (Piece)	9.322 kg

Dimensional drawing





Iridium SGS253

Photometric data



OFPC_SGS253 PC 1xCDO-TT150W CR P1-Polar Outdoor (combined)

OFPC_SGS253 PC 1xCDO-TT150W CR P3-Polar Outdoor (combined)



OFPC1_SGS253 PC 1xCDO-TT150W CR P5X.EPS

OFPC1_SGS253 PC 1xCDO-TT150W CR P7.EPS

