



# Iridium SGS253/453

## SGS253 CDO-TT150W K II CR PC GR SND

IRIDIUM, MASTER CityWhite CDO-TT, 150 W, Closed CT-POT, Polycarbonate bowl/cover

Modular road-lighting luminaires offering a wide choice of optical, electrical and mechanical combinations to make driving safer and more comfortable. Ensures low cost of ownership thanks to its superior optics and low maintenance and installation costs.


### Product data

<b>General Information</b>		<b>Power Consumption</b>	
Lamp family code	CDO-TT [MASTER CityWhite CDO-TT]	150 W	
Gear	CONV [Conventional]	<b>Mechanical and Housing</b>	
Photocell	-	Housing Color	
Product family code	SGS253 [IRIDIUM]	Grey	
Embedded control	-	Overall height	
CE mark	Yes	289 mm	
ENEC mark	ENEC mark	Parts color	
<b>Light Technical</b>		<b>Approval and Application</b>	
Standard tilt angle posttop	5°	Ingress protection code	
Standard tilt angle side entry	5°	IP66 [Dust penetration-protected, jet-proof]	
Number of light sources	1	Mech. impact protection code	
Optical cover type	Polycarbonate bowl/cover	IK08 [5 J vandal-protected]	
Optic type outdoor	Closed CT-POT	Protection class IEC	
<b>Operating and Electrical</b>		Safety class II	
Input Voltage	230 V	<b>Product Data</b>	
		Order product name	
		SGS253 CDO-TT150W K II CR PC GR SND	
		Full product name	
		SGS253 CDO-TT150W K II CR PC GR SND	
		Full product code	
		871155984943000	
		Order code	
		84943000	
		Material Nr. (12NC)	
		910502155518	
		Numerator - Quantity Per Pack	
		1	

Iridium SGS253/453

EAN/UPC - Product/Case	8711559849430
Numerator - Packs per outer box	1
EAN/UPC - Case	8711559849430

Dimensional drawing



Product	A
SGS253 CDO-TT150W K II CR PC GR SND	289 mm

