



Iridium SGS253/453

SGS453 CDO-TT150W K II CR FG AL 7035 SND

IRIDIUM - MASTER CityWhite CDO-TT - 150 W - Closed CT-POT
- Flat glass

Modular road-lighting luminaires offering a wide choice of optical, electrical and mechanical combinations to make driving safer and more comfortable. Ensures low cost of ownership thanks to its superior optics and low maintenance and installation costs.

Product data

General Information	
Number of light sources	1 [1 pc]
Lamp family code	CDO-TT [MASTER CityWhite CDO-TT]
Lamp power	150 W
Kombipack	Lamp(s) included
Gear	CONV [Conventional]
Optical cover/lens type	FG [Flat glass]
Embedded control	No [-]
Light regulation	-
Protection class IEC	Safety class II (II)
Parts color	All parts colored
CE mark	CE mark
ENEC mark	ENEC mark
Optic type outdoor	Closed CT-POT
Colored frame	-
RAL color	Light gray (7035)
Filter coil	-
Photocell	No [-]

Product family code	SGS453 [IRIDIUM]
Light Technical	
Standard tilt angle posttop	5°
Standard tilt angle side entry	5°
Operating and Electrical	
Input Voltage	230 V
Ignitor	SND [Digital semi-parallel]
Mechanical and Housing	
Overall height	190 mm
Dimensions (Height x Width x Depth)	190 x NaN x NaN mm (7.5 x NaN x NaN in)
Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]


Iridium SGS253/453

Product Data

Full product code	871155984952200
Order product name	SGS453 CDO-TT150W K II CR FG AL 7035 SND
EAN/UPC - Product	8711559849522
Order code	84952200
Numerator - Quantity Per Pack	1

Numerator - Packs per outer box	1
Material Nr. (12NC)	910502156418
Net Weight (Piece)	12.322 kg

Dimensional drawing



Iridium SGS253

