



Iridium SGS254/454

SGS254 SON-T150W K II CP GB GR SND

IRIDIUM, SON-T, 150 W, Closed T-POT, Glass bowl/cover

Modular road-lighting luminaire offering a wide choice of optical, electrical and mechanical combinations to make driving safer and more comfortable. Ensures low cost of ownership thanks to its superior optics and low maintenance and installation costs

Product data

General Information	
Lamp family code	SON-T [SON-T]
Gear	CONV [Conventional]
Product family code	SGS254 [IRIDIUM]
CE mark	Yes
ENEC mark	ENEC mark
Light Technical	
Standard tilt angle posttop	5°
Standard tilt angle side entry	5°
Number of light sources	1
Optical cover type	Glass bowl/cover
Optic type outdoor	Closed T-POT
Operating and Electrical	
Input Voltage	230 V
Power Consumption	150 W
Mechanical and Housing	
Housing Color	Grey


Parts color	-
Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Protection class IEC	Safety class II
Product Data	
Order product name	SGS254 SON-T150W K II CP GB GR SND
Full product name	SGS254 SON-T150W K II CP GB GR SND
Full product code	871155984955300
Order code	84955300
Material Nr. (12NC)	910502156718
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711559849553
Numerator - Packs per outer box	1
EAN/UPC - Case	8711559849553

Datasheet, 2023, April 29 data subject to change

Iridium SGS254/454


Dimensional drawing













Product	Α
SGS254 SON-T150W K II CP GB GR SND	319 mm

