



Iridium SGS254/454

SGS454 SON-T250W K II CP GB AL 7035 SND

IRIDIUM, SON-T, 250 W, Closed T-POT, Glass bowl/cover

Modular road-lighting luminaire offering a wide choice of optical, electrical and mechanical combinations to make driving safer and more comfortable. Ensures low cost of ownership thanks to its superior optics and low maintenance and installation costs.

Product data

General Information	
Lamp family code	SON-T [SON-T]
Gear	CONV [Conventional]
Product family code	SGS454 [IRIDIUM]
CE mark	Yes
ENEC mark	ENEC mark

Light Technical	
Standard tilt angle posttop	5°
Standard tilt angle side entry	5°
Number of light sources	1
Optical cover type	Glass bowl/cover
Optic type outdoor	Closed T-POT

Operating and Electrical	
Input Voltage	230 V
Power Consumption	250 W

Mechanical and Housing	
Housing Color	-


Parts color	All parts colored
-------------	-------------------

Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Protection class IEC	Safety class II

Product Data	
Order product name	SGS454 SON-T250W K II CP GB AL 7035 SND
Full product name	SGS454 SON-T250W K II CP GB AL 7035 SND
Full product code	871155984958400
Order code	84958400
Material Nr. (12NC)	910502157018
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711559849584
Numerator - Packs per outer box	1
EAN/UPC - Case	8711559849584

Iridium SGS254/454

Dimensional drawing



Product	A
SGS454 SON-T250W K II CP GB AL 7035 SND	319 mm

