



# Iridium SGS254/454

## SGS454 SON-T400W K II CP FG AL 7035 SND

IRIDIUM - SON-T - 400 W - Closed T-POT - Flat glass

Modular road-lighting luminaire offering a wide choice of optical, electrical and mechanical combinations to make driving safer and more comfortable. Ensures low cost of ownership thanks to its superior optics and low maintenance and installation costs.

### Product data

General Information	
Number of light sources	1 [ 1 pc]
Lamp family code	SON-T [ SON-T]
Lamp power	400 W
Kombipack	Lamp(s) included
Gear	CONV [ Conventional]
Optical cover/lens type	FG [ Flat glass]
Light regulation	-
Electrical circuit protection	-
Protection class IEC	Safety class II (II)
Parts color	All parts colored
Coating	-
CE mark	CE mark
ENEC mark	ENEC mark
Optic type outdoor	Closed T-POT
Colored frame	-
RAL color	Light gray (7035)
Product family code	SGS454 [ IRIDIUM]


Light Technical	
Standard tilt angle posttop	5°
Standard tilt angle side entry	5°
Operating and Electrical	
Input Voltage	230 V
Ignitor	SND [ Digital semi-parallel]
Mechanical and Housing	
Color	-
Dimensions (Height x Width x Depth)	NaN x NaN x NaN mm (NaN x NaN x NaN in)
Approval and Application	
Ingress protection code	IP66 [ Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [ 5 J vandal-protected]
Product Data	
Full product code	871155984961400
Order product name	SGS454 SON-T400W K II CP FG AL 7035 SND
EAN/UPC - Product	8711559849614

## Iridium SGS254/454

Order code	84961400
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	910502157318

Net Weight (Piece)	19.130 kg
--------------------	-----------

### Dimensional drawing



Iridium SGS254

