



Iridium SGS252/452

SGS252 SON-T70W K I OR GB GR SND

IRIDIUM, SON-T, 70 W, Open CT-POT, Glass bowl/cover

Modular road-lighting luminaire offering a wide choice of optical, electrical and mechanical combinations to make driving safer and more comfortable. Ensures low cost of ownership thanks to its superior optics and low maintenance and installation costs


Product data

General Information		Mechanical and Housing	
Lamp family code	SON-T [SON-T]	Housing Color	Grey
Gear	CONV [Conventional]	Mounting device	-
Product family code	SGS252 [IRIDIUM]	Overall height	219 mm
CE mark	Yes	Parts color	-
ENEC mark	ENEC mark		
Light Technical		Approval and Application	
Standard tilt angle posttop	5°	Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Standard tilt angle side entry	5°	Mech. impact protection code	IK08 [5 J vandal-protected]
Number of light sources	1	Protection class IEC	Safety class I
Optical cover type	Glass bowl/cover		
Optic type outdoor	Open CT-POT		
Operating and Electrical		Product Data	
Input Voltage	230 V	Order product name	SGS252 SON-T70W K I OR GB GR SND
Power Consumption	70 W	Full product name	SGS252 SON-T70W K I OR GB GR SND
Cable	-	Full product code	871155985161700
		Order code	85161700
		Material Nr. (12NC)	910502168718
		Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	8711559851617
		Numerator - Packs per outer box	1

Iridium SGS252/452

EAN/UPC - Case	8711559851617
----------------	---------------

Dimensional drawing



Product	A
SGS252 SON-T70W K I OR GB GR SND	219 mm

