



Iridium SGS252/452

SGS252 SON-T100W K I OR GB GR SND

IRIDIUM, SON-T, 100 W, Open CT-POT, Glass bowl/cover

Modular road-lighting luminaire offering a wide choice of optical, electrical and mechanical combinations to make driving safer and more comfortable. Ensures low cost of ownership thanks to its superior optics and low maintenance and installation costs

Product data

General Information	
Lamp family code	SON-T [SON-T]
Gear	CONV [Conventional]
Product family code	SGS252 [IRIDIUM]
CE mark	Yes
ENEC mark	ENEC mark

Light Technical	
Standard tilt angle posttop	5°
Standard tilt angle side entry	5°
Number of light sources	1
Optical cover type	Glass bowl/cover
Optic type outdoor	Open CT-POT

Operating and Electrical	
Input Voltage	230 V
Power Consumption	100 W
Cable	-

Mechanical and Housing	
Housing Color	Grey
Mounting device	-
Overall height	219 mm
Parts color	-


Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Protection class IEC	Safety class I

Product Data	
Order product name	SGS252 SON-T100W K I OR GB GR SND
Full product name	SGS252 SON-T100W K I OR GB GR SND
Full product code	871155985162400
Order code	85162400
Material Nr. (12NC)	910502168818
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711559851624
Numerator - Packs per outer box	1

Iridium SGS252/452

EAN/UPC - Case	8711559851624
----------------	---------------

Dimensional drawing



Product	A
SGS252 SON-T100W K I OR GB GR SND	219 mm

