



# Iridium SGS254/454

## SGS254 SON-T250W K I TP GB GR SND

IRIDIUM, SON-T, 250 W, Open T-POT, Glass bowl/cover

Iridium is a family of road-lighting luminaires designed for three main applications – residential areas and minor roads, major roads and motorways. Its modularity allows the integration of optical or electronic components in order to adapt to the changing demands of road lighting, e.g. the growing demand for white light and controls. Iridium ensures low cost of ownership thanks to its superior optics, dimming and Telemanagement capability, and ease of installation and maintenance. The Iridium luminaire family includes MASTERColour CDM Elite MW, CosmoPolis and LED-enabled versions. It comes in four different sizes – for mounting heights from 3.5 to 12 meters – and is suitable for side-entry and post-top mounting. A full range of brackets ensures visual consistency between the column and the gently rounded luminaire, making Iridium a total solution. Each Iridium luminaire is fully recyclable; only the light source and driver have to be recycled separately.

### Product data

General Information		Mechanical and Housing	
Lamp family code	SON-T [SON-T]	Housing Color	Grey
Product family code	SGS254 [IRIDIUM]		
CE mark	Yes	Approval and Application	
		Protection class IEC	Safety class I
Light Technical		Product Data	
Optical cover type	Glass bowl/cover	Order product name	SGS254 SON-T250W K I TP GB GR SND
Optic type outdoor	Open T-POT	Full product name	SGS254 SON-T250W K I TP GB GR SND
		Full product code	871155985180800
Operating and Electrical		Order code	910502170618
Power Consumption	250 W	Material Nr. (12NC)	910502170618
		Numerator - Quantity Per Pack	1

Iridium SGS254/454

EAN/UPC - Product/Case	8711559851808
Numerator - Packs per outer box	1
EAN/UPC - Case	8711559851808

Dimensional drawing

