



Iridium SGS254/454

SGS254 SON-T400W K I TP GB GR SND

IRIDIUM, SON-T, 400 W, Open T-POT, Glass bowl/cover

Modular road-lighting luminaire offering a wide choice of optical, electrical and mechanical combinations to make driving safer and more comfortable. Ensures low cost of ownership thanks to its superior optics and low maintenance and installation costs.


Product data

General Information	
Lamp family code	SON-T [SON-T]
Gear	CONV [Conventional]
Product family code	SGS254 [IRIDIUM]
Embedded control	-
CE mark	Yes
ENEC mark	ENEC mark
Light Technical	
Standard tilt angle posttop	5°
Standard tilt angle side entry	5°
Number of light sources	1
Optical cover type	Glass bowl/cover
Optic type outdoor	Open T-POT
Operating and Electrical	
Input Voltage	230 V
Power Consumption	400 W
Mechanical and Housing	
Housing Color	Grey

Parts color	-
Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Protection class IEC	Safety class I
Product Data	
Order product name	SGS254 SON-T400W K I TP GB GR SND
Full product name	SGS254 SON-T400W K I TP GB GR SND
Full product code	871155985182200
Order code	85182200
Material Nr. (12NC)	910502170818
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711559851822
Numerator - Packs per outer box	1
EAN/UPC - Case	8711559851822

Iridium SGS254/454

Dimensional drawing



Product	A
SGS254 SON-T400W K I TP GB GR SND	319 mm

