



Modena

SGP682 E40 II CP GB AL 3027

MODENA G, E40, Safety class II, Closed T-POT, Glass bowl/cover, Raspberry red (RAL3027)

Modena is a road-lighting luminaire that combines elegance and excellent lighting performance. Its fluid, rounded form gives it a strong and distinctive visual character. Modena offers a wide choice of optical, electrical and mechanical options to satisfy all road applications. It allows considerable energy savings (dimming with standard dimming devices or stand-alone Lumistep and Chronosense systems; electronic ballast or Telemanagement system) and is easy to install and maintain. The Modena family accommodates CosmoPolis white-light technology and LED-enabled versions and comes in three sizes – for mounting heights from 3.5 to 12 meters. Each Modena luminaire is fully recyclable; only the light source and driver have to be recycled separately.


Product data

General Information		Optic type outdoor	
Cap-Base	E40 [E40]	Closed T-POT	
Gear	E [Empty, without gear]	Mechanical and Housing	
Product family code	SGP682 [MODENA G]	Housing Color	RAL (to be defined)
CE mark	Yes	Overall height	303 mm
ENEC mark	ENEC mark	Parts color	All parts colored
Light Technical		Approval and Application	
Standard tilt angle posttop	5°	Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Standard tilt angle side entry	0°	Mech. impact protection code	IK08 [5 J vandal-protected]
Number of light sources	1	Protection class IEC	Safety class II
Optical cover type	Glass bowl/cover		

Product Data	
Order product name	SGP682 E40 II CP GB AL 3027
Full product name	SGP682 E40 II CP GB AL 3027
Full product code	872790060279100
Order code	60279100
Material Nr. (12NC)	910502270318

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900602791
Numerator - Packs per outer box	1
EAN/UPC - Case	8727900602791

Dimensional drawing



Product
SGP682 E40 II CP GB AL 3027

