



TCW060

TCW060 1xTL-D36W HF

1 pc - MASTER TL-D - 36 W - Electronic high-frequency

Designed for use in demanding environments, TCW060 is an economical, compact waterproof luminaire. Dedicated versions are available for TL-D and TL5 lamps. Ingress-protected to a level of IP65 and operating solely on electronic gear, this is a competitive energy-saving solution for wet spaces – at the same cost as an electromagnetic solution. A flexible ceiling clip facilitates easy installation and maintenance.

Product data

General Information		Warranty period	
Number of light sources	1 [1 pc]	Warranty period	3 years
Lamp family code	TL-D [MASTER TL-D]	Constant light output	No
Beam angle of light source	- °	Number of products on MCB	15
Lamp power	36 W	Unified glare rating CEN	25
Lamp colour code	-	Operating and Electrical	
Kombipack	-	Input voltage	220 to 240 V
Number of gear units	1 unit	Input frequency	50 to 60 Hz
Gear	HF [Electronic high-frequency]	Initial CLO power consumption	Not applicable W
Optical cover/lens type	PCP [Polycarbonate bowl/cover prismatic]	Inrush current	15 A
Emergency lighting	No [-]	Inrush time	0.37 ms
Connection	SI [Screw connection block]	Power factor (min.)	0.9
Cable	-	Controls and Dimming	
Protection class IEC	Safety class I (I)	Dimmable	No
Glow-wire test	650/5 [Temperature 650 °C, duration 5 s]	Mechanical and Housing	
Flammability mark	NO [-]	Reflector material	Steel
Country version	NO [Norway]	Optic material	Polycarbonate
CE mark	CE mark		
ENEC mark	-		

