



Vivara LED

BGC136 RDLM2000-/830 220-240V GN

Vivara LED, LED module RDLM 2000, 830 warm white, 220/240 V, Green

Vivara LED is an economical, vandal-resistant and ‘green’ bollard range for ground-mounting applications. It comes in a choice of two sizes – both with the energy-efficient, long-lasting Fortimo RDLM LED module inside. The internal louver ensures glare-free light distribution. Anticipating environmental legislation, no PVC was used in this product, thus making it a green solution. Economical, robust, using green materials, delivering comfortable light, maintenance-free... what more could we want from a bollard?

Product data

General Information	
Lamp family code	RDLM2000 [LED module RDLM 2000]
Light source replaceable	No
Driver included	Yes
Product family code	BGC136 [Vivara LED]
Lighting Technology	LED
CE mark	Yes
ENEC mark	-
Light Technical	
Luminous Flux	2,000 lm
Luminous Efficacy (rated) (Nom)	32 lm/W
Color rendering index (CRI)	80
Light source color	830 warm white

Operating and Electrical	
Input Voltage	220/240 V
Line Frequency	50 to 60 Hz
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Housing Color	Green
Approval and Application	
Ingress protection code	IP54 [Dust accumulation-protected, splash-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]

Initial Performance (IEC Compliant)	
Init. Color Rendering Index Tolerance	+/-2
Product Data	
Order product name	BGC136 RDLM2000-/830 220-240V GN
Full product name	BGC136 RDLM2000-/830 220-240V GN
Full product code	871794389387400
Order code	89387400

Material Nr. (12NC)	910503677118
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8717943893874
Numerator - Packs per outer box	1
EAN/UPC - Case	8717943893874

Dimensional drawing

