



Vivara LED

BGC137 RDLM2000-/830 220-240V GN

Vivara LED, LED module RDLM 2000, 830 warm white, 220/240 V, Green

Vivara LED is an economical, vandal-resistant and 'green' bollard range for ground-mounting applications. It comes in a choice of two sizes – both with the energy-efficient, long-lasting Fortimo RDLM LED module inside. The internal louver ensures glare-free light distribution. Anticipating environmental legislation, no PVC was used in this product, thus making it a green solution. Economical, robust, using green materials, delivering comfortable light, maintenance-free... what more could we want from a bollard?

Product data

| General Information | | Operating and Electrical | |
|---------------------------------|---------------------------------|------------------------------|--|
| Lamp family code | RDLM2000 [LED module RDLM 2000] | Input Voltage | 220/240 V |
| Light source replaceable | No | Line Frequency | 50 to 60 Hz |
| Driver included | Yes | Controls and Dimming | |
| Product family code | BGC137 [Vivara LED] | Dimmable | No |
| Lighting Technology | LED | Mechanical and Housing | |
| CE mark | Yes | Housing Color | Green |
| ENEC mark | - | Approval and Application | |
| Light Technical | | Ingress protection code | IP54 [Dust accumulation-protected, splash-proof] |
| Luminous Flux | 2,000 lm | Mech. impact protection code | IK08 [5 J vandal-protected] |
| Luminous Efficacy (rated) (Nom) | 32 lm/W | | |
| Color rendering index (CRI) | 80 | | |
| Light source color | 830 warm white | | |

| | |
|--|----------------------------------|
| Initial Performance (IEC Compliant) | |
| Init. Color Rendering Index Tolerance | +/-2 |
| Product Data | |
| Order product name | BGC137 RDLM2000-/830 220-240V GN |
| Full product name | BGC137 RDLM2000-/830 220-240V GN |
| Full product code | 871794389389800 |
| Order code | 89389800 |

| | |
|---------------------------------|---------------|
| Material Nr. (12NC) | 910503677318 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8717943893898 |
| Numerator - Packs per outer box | 1 |
| EAN/UPC - Case | 8717943893898 |

Dimensional drawing

