



TCW060

TCW060 2xTL-D36W HF FR

2, MASTER TL-D, 36 W, 72 W, HF Performer

Designed for use in demanding environments, TCW060 is an economical, compact waterproof luminaire. Dedicated versions are available for TL-D and TL5 lamps. Ingress-protected to a level of IP65 and operating solely on electronic gear, this is a competitive energy-saving solution for wet spaces – at the same cost as an electromagnetic solution. A flexible ceiling clip facilitates easy installation and maintenance.

Product data

General Information		
Lamp family code	TL-D [MASTER TL-D]	
Number of gear units	1 unit	
Gear	HFP [HF Performer]	
Service tag	Yes	
CE mark	Yes	
Warranty period	3 years	
Flammability mark	-	
ENEC mark	-	
Glow-wire test	Temperature 650 °C, duration 5 s	
EU RoHS compliant	Yes	
Light Technical		
Correlated Color Temperature (Nom)	-	
Color rendering index (CRI)	-	
Number of light sources	2	
Beam angle of light source	- degree(s)	
Light source color	-	
Optical cover type	Polycarbonate bowl/cover prismatic	

Luminaire light beam spread	-	
Unified glare rating CEN	25	
Operating and Electrical		
Input Voltage	220 to 240 V	
Line Frequency	50 to 60 Hz	
Initial CLO power consumption	Not applicable W	
Inrush current	20 A	
Inrush time	0.37 ms	
Power Consumption	36 72 W	
Power Factor (Fraction)	0.9	
Connection	Screw connection block 3-pole	
Cable	-	
Number of products on MCB of 16 A type B 13		
Temperature		
Ambient temperature range	-15 to +25 °C	

TCW060

Controls and Dimming		
Dimmable	No	
Constant light output	No	

Mechanical and Housing

Reflector material	Steel	
Optic material	Polycarbonate	
Optical cover material	Polycarbonate	
Housing Color	Grey	
Overall length	1,270 mm	
Overall width	136 mm	
Overall height	90 mm	
Dimensions (Height x Width x Depth)	90 x 136 x 1270 mm	

Over Time Performance (IEC Compliant)		
Driver failure rate at 5000 h	0.01 %	
Application Conditions		
Maximum dim level	Not applicable	
Suitable for random switching	Yes	
Product Data		
Order product name	TCW060 2xTL-D36W HF FR	
Full product name	TCW060 2xTL-D36W HF FR	
Full product code	871794389424699	
Order code	910503679418	
Material Nr. (12NC)	910503679418	
Numerator - Quantity Per Pack	1	
EAN/UPC - Product/Case	8717943894246	
Numerator - Packs per outer box	6	
EAN/UPC - Case	8717943894284	

Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Power consumption tolerance

+/-10%

Dimensional drawing



Product	А	В
TCW060 2xTL-D36W HF FR	900 mm	1,270 mm



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.