



ArchiPoint iColor

ArchiPoint iColor Powercore, Translucent Dome Lens with Conduit Mounting Base, M25 (metric size conduit)

ArchiPoint iColor Powercore, Translucent Dome Lens with Conduit Mounting Base, M25 (metric size conduit)

ArchiPoint iColor Powercore is a daylight-visible, exterior-rated LED point of light ideally suited for a range of direct-view and beacon applications, as well as for accent applications such as path and marker lighting. These versatile low-profile fixtures display large-scale video, graphics, and intricately designed dynamic effects in a host of settings, including architectural, retail, and entertainment installations. ArchiPoint iColor Powercore offers high-intensity output with the efficiency and cost-effectiveness of Powercore technology in a rugged aluminum housing. Powercore delivers line voltage and data to fixtures over a single cable, dramatically simplifying installation and lowering total system cost.

Product data


General information		Accessory PFC	
Lamp family code	LED-HB [LED High Brightness]	ZCP780	
Light source colour	Red, green and blue	Operating and electrical	
Light source replaceable	No	Input Voltage	100 to 240 V
Driver included	Yes	Input frequency	50 to 60 Hz
Optical cover/lens type	TSDM [Transparent dome]	Controls and dimming	
Luminaire light beam spread	150°	Dimmable	No
Protection class IEC	Safety class I (I)	Mechanical and housing	
CE mark	CE mark	Housing material	Aluminum die-cast
UL mark	UL mark	Optic material	Polycarbonate
CCC mark	-		

Colour	Silver
Approval and application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Energy Efficiency Class	G
Mech. impact protection code	IK10 [20 J vandal-resistant]
Vibration standard	Complies with ANSI C136.31, 3G
FCC mark	FCC Class A
Vibration rating	Complies with ANSI C136.31, 3G
	953156
Initial performance (IEC compliant)	
Initial luminous flux (system flux)	501 lm
Initial LED luminaire efficacy	17.6 lm/W
Initial input power	25 W
Over time performance (IEC compliant)	
Lumen Maintenance 50% at 25 °C	100000
Reported	
Lumen Maintenance 50% at 50 °C	70000
Reported	
Lumen Maintenance 70% at 25 °C	70000
Reported	


Lumen Maintenance 70% at 50 °C	40000
Reported	
Application conditions	
Ambient temperature range	-40 to +50 °C
Product data	
Full product code	871829138149599
Order product name	BCP780 LED-HB/RGB 100-240V TS DM SI CE UL
EAN/UPC – product	8718291381495
Order code	123-000022-00
SAP numerator – quantity per pack	1
Numerator – packs per outer box	4
SAP material	910503702579
Net Weight (Piece)	1.500 kg
Commercial Code	123-000022-00
Catalogue number description	ArchiPoint iColor Powercore, Translucent Dome Lens with Conduit Mounting Base, M25 (metric size conduit)




Dimensional drawing




BCP780 LED-HB/RGB 100-240V TS DM SI CE UL



BCP780 LED-HB/RGB 100-240V TS DM SI CE UL




BCP780 LED-HB/RGB 100-240V TS DM SI CE UL



BCP780 LED-HB/RGB 100-240V TS DM SI CE UL

Dimensional drawing



BCP780 LED-HB/RGB 100-240V TSDM SI CE UL

