**PHILIPS** Lighting



# ColorGraze MX Powercore

## ColorGraze MX Powercore, RGB, 15° x 30° Beam Angle, 1219 mm (4 ft)

ColorGraze MX Powercore, RGB, 15° x 30° Beam Angle, 1219 mm (4 ft)

Many architectural structures need a linear fixture capable of illuminating multiple storeys with minimal setback. Property owners/end users need a controllable product capable of dynamic illumination to draw attention to their establishments and emphasize their brands. Graze MX Powercore is capable of illuminating over 20 meters at very close setback distances. Powercore technology enables simple installation and long product run lengths.

#### **Product data**

General Information	
Lamp family code	LED-HB [ LED High Brightness]
Light source colour	RGB
Light source replaceable	No
Driver included	Yes
Luminaire light beam spread	15° x 30°
Protection class IEC	Safety class I (I)
CE mark	CE mark
UL mark	UL and cUL mark
Lifetime to 70% luminous flux	100000 h
Operating and Electrical	
Input Voltage	100 to 277 V

Input frequency	50 to 60 Hz
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Housing material	Aluminum extruded
Optical cover/lens material	Polycarbonate
Length	1219 mm
Colour	Aluminum
Approval and Application	
Ingress protection code	IP66 [ Dust penetration-protected, jet-proof]

### **ColorGraze MX Powercore**

Mech. impact protection code	IK10 [ 20 J vandal-resistant]
Vibration standard	Not compliant to ANSI C136.31, 3G. Special
	orders are available to conform to the
	standard. Please contact your Color Kinetics
	Lighting Sales rep for custom configurations.
Vibration rating	Not compliant to ANSI C136.31, 3G. Special
	orders are available to conform to the
	standard. Please contact your Color Kinetics
	Lighting Sales rep for custom configurations.
Initial Performance (IEC Complia	ant)
Initial input power	80 W
Over Time Performance (IEC Cor	npliant)
Lumen Maintenance 50% at 25 °C	100000
Calculated	
Lumen Maintenance 50% at 25 °C	100000
Reported	
Lumen Maintenance 50% at 50 °C	80000
Calculated	
Lumen Maintenance 50% at 50 °C	80000
Reported	
Lumen Maintenance 70% at 25 °C	100000
Calculated	
Lumen Maintenance 70% at 25 °C	80000

Lumen Maintenance 70% at 50 °C	91000
Calculated	
Lumen Maintenance 70% at 50 °C	60000
Reported	
Application Conditions	
Ambient temperature range	-20 to +50 °C
Product Data	
Full product code	871829160378800
Order product name	BCS459 15x30 RGB L1219
EAN/UPC – product	8718291603788
Order code	123-000079-17
SAP numerator – quantity per pack	1
Numerator – packs per outer box	1
SAP material	910503703344
SAP net weight (piece)	4.700 kg
Commercial Code	123-000079-17
Catalogue number description	ColorGraze MX Powercore, RGB, 15° x 30°
	Beam Angle, 1219 mm (4 ft)



#### Dimensional drawing

Reported



#### ColorGraze MX Powercore



© 2021 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

www.lighting.philips.com 2021, May 13 - data subject to change