



Vaya Flood LP

BCP412 18xLED-HB/5000 100-240 20 CE CQC

18 pcs - LED High Brightness - Medium beam angle 20°

Vaya Flood LP (gen2) is a reliable and cost effective LED flood lighting solution for both interior and exterior use that minimizes the initial investment, while providing exceptional flexibility to create eye-catching flood, wash and accent lighting effects. A wide choice of beam angles and color options let you bring a property to life with either static or dynamically changing colors. Extended light throw and high efficacy set this compact & robust luminaire apart. Its integrated power and adjustable tilt angle make this product versatile and easy to use.

Product data


General Information		Light Technical	
Number of light sources	18 pcs	Standard tilt angle posttop	0°
Lamp family code	LED-HB [LED High Brightness]	Standard tilt angle side entry	0°
Light source replaceable	No	Operating and Electrical	
Driver included	Yes	Input Voltage	100 to 240 V
Optical cover/lens type	Flat glass	Input Frequency	50 to 60 Hz
Protection class IEC	Safety class I	Controls and Dimming	
Type description	-	Dimmable	Yes
CE mark	CE mark	Mechanical and Housing	
ENEC mark	ENEC mark	Housing Material	Aluminum
UL mark	UL mark	Optical cover/lens material	Glass
CQC mark	CQC-mark	Approval and Application	
Lifetime to 70% luminous flux	50000 h	Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Optic type outdoor	Medium beam angle 20°		
PSE mark	No		
RoHS mark	-		
WEEE mark	-		

Vaya Flood LP

Mech. impact protection code	IK06 [1 J]
Initial Performance (IEC Compliant)	
Initial LED luminaire efficacy	45 lm/W
Init. Corr. Color Temperature	5000 K
Init. Color Rendering Index	80
Initial input power	44 W
Application Conditions	
Ambient temperature range	-20 to +40 °C
Product Data	
Full product code	871829138314799

Order product name	BCP412 18xLED-HB/5000 100-240 20 CE CQC
EAN/UPC - Product	8718291383147
Order code	910503703962
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	910503703962
Net Weight (Piece)	2.770 kg

Dimensional drawing



Vaya

