



LuxSpace, recessed

DN571B LED40S/830 PSD-VLC-E C WH

LUXSPACE 2 COMPACT DEEP - LED Module, system flux 4000 lm - 830 warm white - Power supply unit with DALI interface, DC compatible, external - High-gloss mirror - White RAL 9003

Customers are looking to optimize all their resources, and that means not just their running costs (energy, etc.) but also their human resources. Energy savings are therefore a priority, but they must not have an adverse effect on the well-being of employees, who need a pleasant environment in order to be more productive, or on customers, who want to enjoy their shopping experience. LuxSpace provides the perfect combination of efficiency, light comfort and design, without compromising on lighting performance (color rendering and color uniformity). It offers a wide choice of options for creating the desired ambience, no matter the application. For office applications LuxSpace supports the general feeling of health and wellbeing having dedicated Tunable White products

Product data

General Information			
Number of light sources	1 pc	Optical cover/lens type	-
Lamp family code	LED40S [LED Module, system flux 4000 lm]	Luminaire light beam spread	70°
Light source color	830 warm white	Emergency lighting	-
Cap-Base	- [-]	Control interface	DALI
Light source replaceable	No	Connection	Push-in connector and pull relief
Number of gear units	1 unit	Cable	-
Gear	-	Protection class IEC	Safety class II
Driver/power unit/transformer	Power supply unit with DALI interface, DC compatible, external	Glow-wire test	Temperature 850 °C, duration 5 s
Driver included	Yes	Flammability mark	For mounting on normally flammable surfaces
Optic type	High-gloss mirror	CE mark	CE mark
		ENEC mark	ENEC mark

LuxSpace, recessed

UL mark	-
Warranty period	5 years
Decorative accessories	-
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore the median useful life (B50) value also represents the B10 value.
Constant light output	No
Number of products on MCB of 16 A type B	24
Product family code	DN571B [LUXSPACE 2 COMPACT DEEP]
Unified glare rating CEN	22

Light Technical

Optical cover/lens type accessory	-
-----------------------------------	---

Operating and Electrical

Input Voltage	220 to 240 V
Input Frequency	50 to 60 Hz
Control signal voltage	0-16 V DC DALI
Inrush current	20.4 A
Inrush time	0.195 ms
Power Factor (Min)	0.9

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Housing configuration	Basic version
Housing Material	Aluminum die cast
Reflector material	Polycarbonate aluminum coated
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	Steel
Optical cover/lens finish	Frosted
Overall height	119 mm
Overall diameter	214 mm
Color	White RAL 9003

Dimensions (Height x Width x Depth)	119 x NaN x NaN mm (4.7 x NaN x NaN in)
-------------------------------------	-----------------------------------------

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]

Initial Performance (IEC Compliant)

Initial luminous flux (system flux)	4100 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	121 lm/W
Init. Corr. Color Temperature	3000 K
Init. Color Rendering Index	>80
Initial chromaticity	(0.43, 0.40) SDCM <3
Initial input power	34 W
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)


Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L90

Application Conditions

Ambient temperature range	+10 to +25 °C
Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	Yes


Product Data

Full product code	871829194130900
Order product name	DN571B LED40S/830 PSD-VLC-E C WH
EAN/UPC - Product	8718291941309
Order code	910503706645
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	910503706645
Net Weight (Piece)	1.080 kg



LuxSpace, recessed

Dimensional drawing



LuxSpace gen2 DN570B-DN572B

