



# CitySoul gen2 LED Large

### BRP531 GRN106-/740 I DM FG CO GR D9 60S

CitySoul gen2 Large, LED GreenLine 10600 lm, Distribution medium, Flat glass

CitySoul gen2 LED is one of the most versatile and inspirational urban street lighting families designed by Philips to date. This highly efficient range delivers excellent lighting levels whilst also providing the right ambiance for all urban application areas, from the outskirts of the city right through to the city center. By evolving the modularity of the CitySoul family and adding new innovations like the Lyre and the Accent bracket, Philips has made this range the ideal toolbox for every urban context. The design is flatter, completely round, and the transitions with the spigot and bracket entirely flush, thereby giving your cityscape a coherent, elegant and discreet identity. Designed around its LED engine, CitySoul gen2 LED is highly efficient and easy to maintain. It comes in two sizes and is suitable for side-entry, post-top, catenary and suspended mounting.

#### **Product data**

General Information	
Lamp family code	GRN106 [LED GreenLine 10600 lm]
Light source replaceable	Yes
Number of gear units	Unit
Driver included	Yes
Remarks	* At extreme ambient temperatures the
	luminaire might automatically dim down to
	protect components
Light source engine type	LED
Product family code	BRP531 [CitySoul gen2 Large]

Lighting Technology	LED
Value ladder	Performance
Embedded control	-
CE mark	Yes
Warranty period	5 years
Flammability mark	=
ENEC mark	ENEC mark
Glow-wire test	Temperature 650 °C, duration 30 s
EU RoHS compliant	Yes
	-

Datasheet, 2023, December 5 data subject to change

# CitySoul gen2 LED Large

Light Technical	
Upwards light output ratio	0.03
Luminous Flux	10.697 lm
Standard tilt angle post-top	0°
Standard tilt angle side entry	0°
Correlated Colour Temperature	4000 K
Luminous efficacy (rated) (nom.)	157 lm/W
Colour rendering index (CRI)	>70
Light source colour	740 neutral white
Optical cover type	Flat glass
Luminaire light beam spread	180°
Optic type outdoor	Distribution medium
	<i>Distribution</i> mediam
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	53 A
Inrush time	0.3 ms
Power Consumption	68 W
Power Factor (Fraction)	0.8
Connection	-
Cable	-
Number of products on MCB of 16 A typ	pe B 11
Temperature	
Ambient temperature range	-40 to +50 °C
Ambient temperature range	40.10.150 C
Controls and Dimming	
Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No
Mechanical and Housing	
Housing material	Aluminium
Reflector material	-
Optic material	Polymethyl methacrylate
Optical cover/lens material	Polymethyl methacrylate
Fixation material	Aluminium
Housing Colour	Grey
Mounting device	Side-entry for diameter 60 mm
Optical cover/lens shape	Convex lens
Optical cover/lens finish	Mask (anti-glare)

Overall length	735 mm	
Overall width	628 mm	
Overall height	106 mm	
Effective projected area	0.029 m²	
Dimensions (height x width x depth)	106 x 628 x 735 mm	
Parts colour	Cover painted	
Approval and Application		
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]	
Mech. impact protection code	IK08 [5 J vandal-protected]	
Surge Protection (Common/Differential)	Luminaire surge protection level up to 6 kV	
	differential mode and 8 kV common mode	
Protection class IEC	Safety class I	
Photobiological risk	Photobiological risk group 1 @200mm to	
	EN62778	
Initial Performance (IEC Compliant)		
Luminous flux tolerance	+/-10%	
Initial chromaticity	(0.38,0.37) SDCM<5	
Power consumption tolerance	+/-10%	
Init. Color Rendering Index Tolerance	+/-2	
Over Time Performance (IEC Compliant)		
Driver failure rate at 5,000 hours	0.15 %	
Application Conditions		
Maximum dim level	20%	
Product Data		
Order product name	BRP531 GRN106-/740 I DM FG CO GR D9	
	60S	
Full product name	BRP531 GRN106-/740 I DM FG CO GR D9	
	60S	
Full EOC	871869661340500	
Order code	61340500	
Material no. (12 NC)	910505016880	
SAP numerator – quantity per pack	1	
EAN/UPC — Product/Case	8718696613405	
Numerator – packs per outer box	1	
EAN/UPC - Case	8718696613405	

## CitySoul gen2 LED Large

#### Dimensional drawing



