



# CitySoul gen2 LED Large

## BRP531 GRN185-/740 I DM FG CO GR D9 60S

CitySoul gen2 Large, LED GreenLine 18500 lm, Distribution medium, Flat glass

CitySoul gen2 LED is one of the most versatile and inspirational urban street lighting families designed by Philips to date. This highly efficient range delivers excellent lighting levels whilst also providing the right ambiance for all urban application areas, from the outskirts of the city right through to the city center. By evolving the modularity of the CitySoul family and adding new innovations like the Lyre and the Accent bracket, Philips has made this range the ideal toolbox for every urban context. The design is flatter, completely round, and the transitions with the spigot and bracket entirely flush, thereby giving your cityscape a coherent, elegant and discreet identity. Designed around its LED engine, CitySoul gen2 LED is highly efficient and easy to maintain. It comes in two sizes and is suitable for side-entry, post-top, catenary and suspended mounting.

#### **Product data**

General Information	
Lamp family code	GRN185 [LED GreenLine 18500 lm]
Light source replaceable	Yes
Number of gear units	1 unit
Driver included	Yes
Remarks	* At extreme ambient temperatures the
	luminaire might automatically dim down to
	protect components
Light source engine type	LED
Product family code	BRP531 [CitySoul gen2 Large]

Lighting Technology	LED
Value ladder	Performance
Embedded control	-
CE mark	Yes
Warranty period	5 years
Flammability mark	-
ENEC mark	ENEC mark
Glow-wire test	Temperature 650 °C, duration 30 s
EU RoHS compliant	Yes

Datasheet, 2023, April 29 data subject to change

# CitySoul gen2 LED Large

Light Technical	
	0.03
Upward light output ratio	0.03
Luminous Flux	14,995 lm
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	115 lm/W
Color rendering index (CRI)	>70
Number of light sources	64
Light source color	740 neutral white
Optical cover type	Flat glass
Luminaire light beam spread	180°
Optic type outdoor	Distribution medium
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	53 A
Inrush time	0.3 ms
Power Consumption	130 W
Power Factor (Fraction)	0.8
Connection	-
Cable	-
Number of products on MCB of 16 A type B	11
Temperature	
Ambient temperature range	-40 to +50 °C
Controls and Dimming	
Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No
Mechanical and Housing	
Housing Material	Aluminum
Reflector material	-
Optic material	Polymethyl methacrylate
Optical cover material	Polymethyl methacrylate
Fixation material	Aluminum
Housing Color	Grey
Mounting device	Side-entry for diameter 60 mm
Outiled accomplished	Convoy long
Optical cover shape	Convex lens

Optical cover finish	Mask (anti-glare)
Overall length	735 mm
Overall width	628 mm
Overall height	106 mm
Effective projected area	0.029 m²
Dimensions (Height x Width x Depth)	106 x 628 x 735 mm
Parts color	Cover painted
Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Luminaire surge protection level until 6 kV
	differential mode and 8 kV common mode
Protection class IEC	Safety class I
Photobiological risk	Photobiological risk group 1 @200mm to
	EN62778
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38,0.37) SDCM<5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2
Over Time Performance (IEC Compli	ant)
Driver failure rate at 5000 h	0.15 %
Application Conditions	
Maximum dim level	10%
Product Data	
Order product name	BRP531 GRN185-/740 I DM FG CO GR D9
	605
	60S
Full product name	BRP531 GRN185-/740 I DM FG CO GR D9
Full product name	
	BRP531 GRN185-/740 I DM FG CO GR D9
Full product name  Full product code  Order code	BRP531 GRN185-/740 I DM FG CO GR D9 60S
Full product code	BRP531 GRN185-/740 I DM FG CO GR D9 60S 871869661344300
Full product code Order code	BRP531 GRN185-/740 I DM FG CO GR D9 60S 871869661344300 61344300
Full product code Order code Material Nr. (12NC) Numerator - Quantity Per Pack	BRP531 GRN185-/740 I DM FG CO GR D9 60S 871869661344300 61344300 910505016884
Full product code Order code Material Nr. (12NC) Numerator - Quantity Per Pack EAN/UPC - Product/Case	BRP531 GRN185-/740 I DM FG CO GR D9 60S 871869661344300 61344300 910505016884 1 8718696613443
Full product code Order code Material Nr. (12NC) Numerator - Quantity Per Pack	BRP531 GRN185-/740 I DM FG CO GR D9 60S 871869661344300 61344300 910505016884

# CitySoul gen2 LED Large

### Dimensional drawing



