



CityCharm Cordoba

BDS490 GRN80-/830 I S GRB GR 60

CityCharm Cordoba, LED GreenLine 8000 lm, Symmetrical, Spigot for diameter 60 mm

CityCharm Cordoba is designed for use in urban areas where comfortable lighting, ambiance and design play an important role. Its unobtrusive appearance makes it a timeless, future-proof luminaire that is ideal for residential areas, parks, footpaths and cycle lanes, where visual comfort and maximum efficiency are key. CityCharm offers a choice of two iconic designs (Cordoba and Cone) and various accessories, enabling you to create a lighting solution that carries your signature, both by day and by night. CityCharm luminaires are also available as a complete set, with a choice of dedicated poles and brackets.

Product data

General Information	
Lamp family code	GRN80 [LED GreenLine 8000 lm]
Light source replaceable	Yes
Number of gear units	1 unit
Gear	EB [Electronic]
Driver included	Yes
Remarks	* At extreme ambient temperatures the
	luminaire might automatically dim down to
	protect components
Light source engine type	LED
Service tag	Yes
Product family code	BDS490 [CityCharm Cordoba]
Lighting Technology	LED
Value ladder	Performance
Embedded control	-

CE mark	Yes
Warranty period	5 years
Flammability mark	-
ENEC mark	ENEC mark
Glow-wire test	Temperature 650 °C, duration 30 s
EU RoHS compliant	Yes
Light Technical	
Upward light output ratio	0.03
Luminous Flux	6,112 lm
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	102 lm/W
Color rendering index (CRI)	≥80


Datasheet, 2023, April 29 data subject to change

CityCharm Cordoba

Number of light sources	40
Light source color	830 warm white
Optical cover type	Polycarbonate bowl/cover
Luminaire light beam spread	360°
Optic type outdoor	Symmetrical
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	80 A
Inrush time	15 ms
Power Consumption	60 W
Power Factor (Fraction)	0.9
Connection	Flying leads/wires
Cable	Cable 0.2 m without plug
Number of products on MCB of 16 A t	type B 11
Temperature	
Ambient temperature range	-40 to +50 °C
Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit regulating
Control interface	-
Constant light output	No
Mechanical and Housing	
Housing Material	Aluminum
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Aluminum
Housing Color	Grey
Mounting device	Spigot for diameter 60 mm
Optical cover shape	Hemispherical
Optical cover finish	Clear
Overall height	529 mm

Overall diameter	556 mm
Effective projected area	0.1124 m²
Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK10 [20 J vandal-resistant]
Surge Protection (Common/Differential)	Luminaire surge protection level until 6 kV
	differential mode and 8 kV common mode
Protection class IEC	Safety class I
Photobiological risk	Photobiological risk group 1 @200mm to
	EN62778
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.430, 0.400) SDCM <3
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2
Over Time Performance (IEC Compli	ant)
Driver failure rate at 5000 h	0.05 %
Application Conditions	
Maximum dim level	Not applicable
Product Data	
Order product name	BDS490 GRN80-/830 I S GRB GR 60
Full product name	BDS490 GRN80-/830 I S GRB GR 60
Full product code	871869692153100
Order code	92153100
Material Nr. (12NC)	910505017169
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696921531
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696921531

Dimensional drawing



CityCharm Cordoba



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.