



Iridium SGS253/453

SGS253 SON-T150W K II CX GB GR SND

IRIDIUM, SON-T, 150 W, Closed XT-POT, Glass bowl/cover

Modular road-lighting luminaires offering a wide choice of optical, electrical and mechanical combinations to make driving safer and more comfortable. Ensures low cost of ownership thanks to its superior optics and low maintenance and installation costs.

Product data

General Information	
Lamp family code	SON-T [SON-T]
Product family code	SGS253 [IRIDIUM]
CE mark	Yes
Light Technical	
Optical cover type	Glass bowl/cover
Optic type outdoor	Closed XT-POT
Operating and Electrical	
Power Consumption	150 W
Mechanical and Housing	
Housing Color	Grey

Approval and Application	
Protection class IEC	Safety class II
Product Data	
Order product name	SGS253 SON-T150W K II CX GB GR SND
Full product name	SGS253 SON-T150W K II CX GB GR SND
Full product code	871794386421800
Order code	86421800
Material Nr. (12NC)	910721401430
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8717943864218
Numerator - Packs per outer box	1
EAN/UPC - Case	8717943864218

Iridium SGS253/453

Dimensional drawing

