



Mini 300 Stealth DGP333

DGP333 CDM-T150W/830 IC OR SI

DGP333, MASTERColour CDM-T, 150 W, Open CT-POT

Mini 300 Stealth is a range of extremely efficient luminaires – with a choice of HID or LED light sources – that can be used to illuminate large areas with direct and/or indirect light. Optimal lighting results are achieved thanks to the good balance of horizontal and vertical light levels combined with the white light and good color rendering of the light sources. Mini 300 Stealth is supplied with an asymmetric medium-beam, wide or narrow-beam reflector. It is also available with the road-lighting POT optic, making it suitable for site perimeter, parking and open area lighting. The light source is shielded by a patented louver system, minimizing glare. Mini 300 Stealth is suitable for pole mounting (DGP333), wall mounting (DWP333) or floodlighting (DVP333). Mini300 Stealth is also available in LED versions for pole mounting (BGP333), wall mounting (BWP333) or floodlighting (BVP333). Within the Mini 300 product family there is also a dedicated under-canopy version (Mini 300 Cube and Mini 300 LED), e.g. for petrol-station applications.

Product data

General Information	
Lamp family code	CDM-T [MASTERColour CDM-T]
Gear	CONV [Conventional]
Product family code	DGP333 [DGP333]
CE mark	Yes
Flammability mark	-
ENEC mark	ENEC mark
Glow-wire test	Temperature 850 °C, duration 5 s

Light Technical	
Number of light sources	1
Light source color	830 warm white
Optic type outdoor	Open CT-POT

Operating and Electrical	
Input Voltage	230 V (default) or 240 V
Power Consumption	150 W

Mini 300 Stealth DGP333

Mechanical and Housing	
Housing Color	Silver
Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK09 [10 J]
Protection class IEC	Safety class I
Product Data	
Order product name	DGP333 CDM-T150W/830 IC OR SI

Full product name	DGP333 CDM-T150W/830 IC OR SI
Full product code	869065338572600
Order code	38572600
Material Nr. (12NC)	910925493312
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8690653385726
Numerator - Packs per outer box	1
EAN/UPC - Case	8690653385726

Dimensional drawing

