



Malaga SGS101

SGS101 SON-T70W II MR FG SKD 42/60

MALAGA, SON-T, 70 W, Safety class II, Moveable reflector, Flat glass, Universal for diameter 42 to 60 mm

Malaga is a versatile road-lighting luminaire. It offers modern styling and quality lighting for safe and comfortable driving, and for area illumination, with low investment and maintenance costs. The optical system has been designed to deliver good beam control and light output. Malaga provides optimal illuminance and good uniformity when the mounting height approximately equals the road width and the mast spacing is approximately 3.5 times the road width. It is suitable for post-top and side-entry mounting; a wall-mounting bracket is also available.

Product data

General Information		Operating and Electrical	
Lamp family code	SON-T [SON-T]	Input Voltage	230 V (default) or 240 V
Cap-Base	E27 [E27]	Power Consumption	70 W
Gear	CONV [Conventional]	Mechanical and Housing	
Photocell	-	Housing Color	Grey
Product family code	SGS101 [MALAGA]	Mounting device	Universal for diameter 42 to 60 mm
CE mark	Yes	Approval and Application	
ENEC mark	ENEC mark	Ingress protection code	IP43/65 [Wire-protected, rain/spray-proof; dust penetration-protected, jet-proof]
Light Technical		Mech. impact protection code	IK08 [5 J vandal-protected]
Standard tilt angle posttop	15°	Protection class IEC	Safety class II
Standard tilt angle side entry	15°	Product Data	
Number of light sources	1	Order product name	SGS101 SON-T70W II MR FG SKD 42/60
Optical cover type	Flat glass		
Optic type outdoor	Moveable reflector		

Malaga SGS101

Full product name	SGS101 SON-T70W II MR FG SKD 42/60
Full product code	872790063647500
Order code	910925702612
Material Nr. (12NC)	910925702612
Numerator - Quantity Per Pack	1

EAN/UPC - Product/Case	8727900636475
Numerator - Packs per outer box	1
EAN/UPC - Case	8727900636475

Dimensional drawing

