



Selenium

SGP340 SON-T150W K I FG SKD 48/60

Selenium LED, SON-T, 150 W, E40, Safety class I, Flat glass, Universal for diameter 48 to 60 mm

Selenium SGP340 is an efficient, ergonomic road-lighting luminaire. Its simple, rounded form reduces its daytime visual impact, allowing it to integrate into any kind of environment. Selenium incorporates the renowned T-POT reflector for excellent optical performance. Energy savings are possible by means of dimming with a switch or stand-alone Chronosense system (without pilot cable). Selenium is suitable for side-entry or post-top mounting, with a choice of three tilt angles for optimal installation (0, 5, 15°).

Product data

General Information	
Lamp family code	SON-T [SON-T]
Cap-Base	E40 [E40]
Gear	CONV [Conventional]
Photocell	-
Product family code	BGP340 [Selenium LED]
Embedded control	-
CE mark	Yes
ENEC mark	-
Light Technical	
Standard tilt angle posttop	5°
Standard tilt angle side entry	0°
Number of light sources	1
Optical cover type	Flat glass

Optic type outdoor	Open T-POT
Operating and Electrical	
Input Voltage	230 to 240 V
Power Consumption	150 W
Mechanical and Housing	
Housing Color	Gray
Mounting device	Universal for diameter 48 to 60 mm
Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Protection class IEC	Safety class I


Selenium

Product Data

Order product name	SGP340 SON-T150W K I FG SKD 48/60
Full product name	SGP340 SON-T150W K I FG SKD 48/60
Full product code	871829106419000
Order code	06419000
Material Nr. (12NC)	910925738912

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291064190
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291064190

Dimensional drawing



Product

SGP340 SON-T150W K I FG SKD 48/60

