



# Malaga SGS101

## SGS101 SON-T50W II MR-AS SKD 42/60

MALAGA, SON-T, 50 W, Safety class II, Moveable reflector with Allen screw, Universal for diameter 42 to 60 mm

Malaga is a versatile road-lighting luminaire. It offers modern styling and quality lighting for safe and comfortable driving, and for area illumination, with low investment and maintenance costs. The optical system has been designed to deliver good beam control and light output. Malaga provides optimal illuminance and good uniformity when the mounting height approximately equals the road width and the mast spacing is approximately 3.5 times the road width. It is suitable for post-top and side-entry mounting; a wall-mounting bracket is also available.

### Product data

General Information	
Lamp family code	SON-T [SON-T]
Cap-Base	E27 [E27]
Gear	CONV [Conventional]
Photocell	-
Product family code	SGS101 [MALAGA]
CE mark	Yes
ENEC mark	ENEC mark
Light Technical	
Standard tilt angle posttop	15°
Standard tilt angle side entry	15°
Number of light sources	1
Optical cover type	Polycarbonate bowl/cover
Optic type outdoor	Moveable reflector with Allen screw

Operating and Electrical	
Input Voltage	230 V (default) or 240 V
Power Consumption	50 W
Mechanical and Housing	
Housing Color	Grey
Mounting device	Universal for diameter 42 to 60 mm
Approval and Application	
Ingress protection code	IP43/65 [Wire-protected, rain/spray-proof; dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Protection class IEC	Safety class II
Product Data	
Order product name	SGS101 SON-T50W II MR-AS SKD 42/60

Malaga SGS101

Full product name	SGS101 SON-T50W II MR-AS SKD 42/60
Full product code	871155926903000
Order code	26903000
Material Nr. (12NC)	910925811712
Numerator - Quantity Per Pack	1

EAN/UPC - Product/Case	8711559269030
Numerator - Packs per outer box	1
EAN/UPC - Case	8711559269030

Dimensional drawing

