



# Malaga SGS101

## SGS101 SON-TPP70W K II MR SKD 42/60A

MALAGA, SON-T PIA Plus, 70 W, Safety class II, Moveable reflector, Universal for diameter 42 to 60 mm adjustable

Malaga is a versatile road-lighting luminaire. It offers modern styling and quality lighting for safe and comfortable driving, and for area illumination, with low investment and maintenance costs. The optical system has been designed to deliver good beam control and light output. Malaga provides optimal illuminance and good uniformity when the mounting height approximately equals the road width and the mast spacing is approximately 3.5 times the road width. It is suitable for post-top and side-entry mounting; a wall-mounting bracket is also available.

### Product data

General Information	
Lamp family code	SON-TPP [SON-T PIA Plus]
Cap-Base	E27 [E27]
Gear	CONV [Conventional]
Photocell	-
Product family code	SGS101 [MALAGA]
CE mark	Yes
ENEC mark	ENEC mark

Light Technical	
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°
Number of light sources	1
Optical cover type	Polycarbonate bowl/cover
Optic type outdoor	Moveable reflector

Operating and Electrical	
Input Voltage	230 V (default) or 240 V
Power Consumption	70 W

Mechanical and Housing	
Housing Color	Grey
Mounting device	Universal for diameter 42 to 60 mm adjustable

Approval and Application	
Ingress protection code	IP43/65 [Wire-protected, rain/spray-proof; dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Protection class IEC	Safety class II

Product Data	
Order product name	SGS101 SON-TPP70W K II MR SKD 42/60A

# Malaga SGS101

Full product name	SGS101 SON-TPP70W K II MR SKD 42/60A
Full product code	871155911977900
Order code	11977900
Material Nr. (12NC)	910925812912
Numerator - Quantity Per Pack	1

EAN/UPC - Product/Case	8711559119779
Numerator - Packs per outer box	1
EAN/UPC - Case	8711559119779

## Dimensional drawing

