



# Malaga SGS101

## SGS101 SON-I-70W-CO K II MR 42/60A

MALAGA, SON-I, 70 W, Safety class II, Moveable reflector,  
Universal for diameter 42 to 60 mm adjustable

Malaga is a versatile road-lighting luminaire. It offers modern styling and quality lighting for safe and comfortable driving, and for area illumination, with low investment and maintenance costs. The optical system has been designed to deliver good beam control and light output. Malaga provides optimal illuminance and good uniformity when the mounting height approximately equals the road width and the mast spacing is approximately 3.5 times the road width. It is suitable for post-top and side-entry mounting; a wall-mounting bracket is also available.

### Product data

General Information		Operating and Electrical	
Lamp family code	SON-I	Input Voltage	230 V (default) or 240 V
Cap-Base	E27 [E27]	Power Consumption	70 W
Gear	CONV [Conventional]	Mechanical and Housing	
Photocell	-	Bulb Finish	Coated glass
Product family code	SGS101 [MALAGA]	Housing Color	Grey
CE mark	Yes	Mounting device	Universal for diameter 42 to 60 mm adjustable
ENEC mark	ENEC mark	Approval and Application	
Light Technical		Ingress protection code	IP43/65 [Wire-protected, rain/spray-proof; dust penetration-protected, jet-proof]
Standard tilt angle posttop	0°	Mech. impact protection code	IK08 [5 J vandal-protected]
Standard tilt angle side entry	0°	Protection class IEC	Safety class II
Number of light sources	1		
Optical cover type	Polycarbonate bowl/cover		
Optic type outdoor	Moveable reflector		

Malaga SGS101

Product Data	
Order product name	SGS101 SON-I-70W-CO K II MR 42/60A
Full product name	SGS101 SON-I-70W-CO K II MR 42/60A
Full product code	871155911978600
Order code	11978600
Material Nr. (12NC)	910925816512

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711559119786
Numerator - Packs per outer box	1
EAN/UPC - Case	8711559119786

Dimensional drawing

