



# Maxos fusion

## LL500Z MB-SW WH

Maxos fusion Acc., White

Maxos fusion is an adaptable LED trunking system that offers an excellent quality of light while more than halving energy costs compared to fluorescent lamps. For retail applications, a family of linear panels, non-linear modules and a spot portfolio can be smoothly integrated into the track backbone to let your merchandise sparkle and stand out. For industrial applications, the focus is on reducing installation and maintenance cost by using fewer linear panels. With the electrical set-up of up to 13 wires, the freedom to position these fixtures as required and the integration of other services/third-party hardware, the system allows you to reduce ceiling clutter. It can also be easily re-configured to accommodate future lay-out changes. The infrastructure is enabled to integrate sensors for data collection, giving you the opportunity to use insightful granular information to support your business.

### Product data

General Information		Material	
Accessory color	White		Steel
Product family code	LL500Z [Maxos fusion Acc.]	Approval and Application	
Value ladder	Specification	Mech. impact protection code	IK00 [No protection]
		Protection class IEC	-
Operating and Electrical		Product Data	
Input Voltage	- V	Order product name	LL500Z MB-SW WH
Line Frequency	- Hz	Full product name	LL500Z MB-SW WH
Mechanical and Housing		Full product code	871869637451199
Overall length	65 mm	Order code	910925864221
Overall width	40 mm	Material Nr. (12NC)	910925864221
Overall height	50 mm	Numerator - Quantity Per Pack	1
Dimensions (Height x Width x Depth)	50 x 40 x 65 mm	EAN/UPC - Product/Case	8718696374511

## Maxos fusion

Numerator - Packs per outer box	40
EAN/UPC - Case	8718696383391

### Dimensional drawing

