



CoreLine recessed

RC134Z CFRM-PLC WH W60L60

Coreline Recessed Acc.

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Recessed range of LED products can be used to replace functional luminaires in general lighting applications. The process of selecting, installing and maintaining is so easy – it's a simple switch.

Warnings and Safety

- The product is IPX0 & as such is not protected against water ingress & as such we strongly recommend that The environment in which The luminaire is to be installed is suitably checked
- If the above advice is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure & product warranty will become void

Product data

General Information	
Angle	-
Accessory color	White
Service tag	Yes
Product family code	RC134Z [Coreline Recessed Acc.]
Value ladder	Performance
Operating and Electrical	
Input Voltage	- V
Line Frequency	- Hz
Mechanical and Housing	
Overall length	630 mm
Overall width	630 mm

Overall height	61 mm
Dimensions (Height x Width x Depth)	61 x 630 x 630 mm
Material	Steel

Approval and Application

Protection class IEC	-
----------------------	---

Product Data

Order product name	RC134Z CFRM-PLC WH W60L60
Full product name	RC134Z CFRM-PLC WH W60L60
Full product code	871869698722300
Order code	98722300
Material Nr. (12NC)	910925864621
Numerator - Quantity Per Pack	1

CoreLine recessed

EAN/UPC - Product/Case	8718696987223
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696987223

Dimensional drawing

