



CoreLine recessed

RC134Z CFRM-PLC WH W60L60

Coreline Recessed Acc.

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Recessed range of LED products can be used to replace functional luminaires in general lighting applications. The process of selecting, installing and maintaining is so easy – it's a simple switch. In addition, Coreline Recessed also provides the option of advanced connectivity and is ready to be connected to IoT based software applications such as Interact Pro.

Warnings and Safety

- The product is IPX0 and as such is not protected against water ingress, so we strongly recommend that the environment in which the luminaire is to be installed is suitably checked
- If the above advice is not taken and the luminaires are subject to water ingress, Philips/Signify cannot guarantee safe failure and product warranty will become void

Product data

General Information		Approval and Application	
Angle	-	Overall width	630 mm
Accessory colour	White	Overall height	61 mm
Product family code	RC134Z [Coreline Recessed Acc.]	Dimensions (height x width x depth)	61 x 630 x 630 mm
Value ladder	Performance	Material	Steel
Operating and Electrical		Approval and Application	
Input Voltage	- V	Protection class IEC	-
Line Frequency	- Hz	Product Data	
Mechanical and Housing		Order product name	RC134Z CFRM-PLC WH W60L60
Overall length	630 mm	Full product name	RC134Z CFRM-PLC WH W60L60
		Full EOC	871869698722300

CoreLine recessed

Order code	98722300
Material no. (12 NC)	910925864621
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696987223

Numerator – packs per outer box	1
EAN/UPC – Case	8718696987223

Dimensional drawing

