



CoreLine recessed

RC134Z CFRM-PLC WH W30L120

Coreline Recessed Acc.

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Recessed range of LED products can be used to replace functional luminaires in general lighting applications. The process of selecting, installing and maintaining is so easy – it's a simple switch. In addition, Coreline Recessed also provides the option of advanced connectivity and is ready to be connected to IoT based software applications such as Interact Pro.

Warnings and Safety

- The product is IPX0 and as such is not protected against water ingress, so we strongly recommend that the environment in which the luminaire is to be installed is suitably checked
- If the above advice is not taken and the luminaires are subject to water ingress, Philips/Signify cannot guarantee safe failure and product warranty will become void

Product data

General Information	
Angle	-
Accessory colour	White
Product family code	RC134Z [Coreline Recessed Acc.]
Value ladder	Performance
Operating and Electrical	
Input Voltage	- V
Line Frequency	- Hz
Mechanical and Housing	
Overall length	1,230 mm

Overall width	330 mm
Overall height	61 mm
Dimensions (height x width x depth)	61 x 330 x 1230 mm
Material	Steel
Approval and Application	
Protection class IEC	-
Product Data	
Order product name	RC134Z CFRM-PLC WH W30L120
Full product name	RC134Z CFRM-PLC WH W30L120
Full EOC	871869698724700

CoreLine recessed

Order code	98724700
Material no. (12 NC)	910925864623
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696987247

Numerator – packs per outer box	1
EAN/UPC – Case	8718696987247

Dimensional drawing

