



Mini 300 LED gen3

ZBP333 CFRM L360 W360 WH

White

Philips Mini 300 LED gen3 luminaires, perfect product design and latest LED technology combination for highly efficient light outputs can turn your petrol station into a branded landmark and help visitors to approach safely in visual comfort. Mini 300 LED gen3, the state-of-the-art LED luminaires with light on demand intelligent motion sensing control system takes energy saving to new levels with dimming, but at the same time, ensuring sufficient lighting for orientation and safety. The light scenarios can be tailored to your preference at the first installation or during the lifespan of the products. The optional Master-Slave combination with a built-in presence and light sensor there's no need for an external sensor and one Master Mini 300 LED gen3 can control up to 6 basic luminaires. Not only will this have a positive impact on your investment, it can also lead to additional energy saving. Mini 300 LED gen3 luminaire is so light that it can be installed effortlessly by one person. Luminaire settings can even be changed from ground level using a smart phone or tablet as a remote control, eliminating the need to work at height. With the free Mini 300 LED App, even the status of the luminaire can be read while standing on the floor. The Mini 300 LED gen3 luminaires in recessed mounted, surface mounted and floodlight versions, which are suitable for undercanopy lighting, is a breakthrough, retrofit solution reduces installation costs.

Product data

General Information		Operating and Electrical	
Angle	0°	Input Voltage	- V
Accessory color	White	Line Frequency	- Hz
Product family code	ZBP333 [Mini 300 LED gen3.ACC]	Mechanical and Housing	
Value ladder	Specification	Overall length	413 mm
		Overall width	413 mm

Mini 300 LED gen3

Overall height	92 mm
Overall diameter	0 mm
Dimensions (Height x Width x Depth)	92 x 413 x 413 mm
Material	Steel

Approval and Application

Ingress protection code	-
Mech. impact protection code	IK08 [5 J vandal-protected]
Protection class IEC	-

Product Data

Order product name	ZBP333 CFRM L360 W360 WH
--------------------	--------------------------

Full product name	ZBP333 CFRM L360 W360 WH
Full product code	871869699768000
Order code	910925865290
Material Nr. (12NC)	910925865290
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696997680
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696997680

Dimensional drawing

