



TCH086

TCH086 TL5-28W/830 HF 220-240V

TL5, 28 W, 830 warm white, Electronic high-frequency, 220 to 240 V $\,$

When it comes to selecting a batten, customers want a trunkable solution that combines safety and lifetime reliability with a slim design and ease of installation – so that they can meet the different requirements of different applications. Our T5 Essential Batten is extremely safe, highly reliable and offers significant energy savings compared with a T8 batten. With its slim housing it is easy to install and conceal in tight spaces, and trunking is straightforward.

Product data

General Information	
Lamp family code	TL5 [TL5]
Gear	HF [Electronic high-frequency]
Service tag	Yes
Light Technical	
Number of light sources	1
Light source color	830 warm white
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Power Consumption	28 W
Approval and Application	
Ingress protection code	IP20 [Finger-protected]

Protection class IEC	Safety class II
Product Data	
Full product code	911400873980
Order product name	TCH086 TL5-28W/830 HF 220-240V
Order code	911400873980
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	24
Material Nr. (12NC)	911400873980
Full product name	TCH086 TL5-28W/830 HF 220-240V
EAN/UPC - Product/Case	8710163288680

TCH086

Dimensional drawing





© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2023, September 4 - data subject to change