



LED Wall Mount

BWS150 LED200/NW PSU 220-240V 7043

LED Low Power, Power supply unit (On/Off)

People want to create a pleasant atmosphere around their property – something that will catch visitors' attention, make them feel good and want to come back again. They would like to be able to create an appealing ambience at minimum cost, though without compromising on the quality of the lighting. Combining a simple round design with reliable lighting performance, this low-cost white-light LED wall fixture with opal diffuser delivers a soft light effect with attractive uniformity.

Product data

General Information		Optical cover type	
Lamp family code	LED-LP [LED Low Power]	Polycarbonate bowl/cover UV-resistant	
Light source replaceable	No	Operating and Electrical	
Number of gear units	1 unit	Input Voltage	220 to 240 V
Driver included	Yes	Line Frequency	50 to 60 Hz
Light source engine type	LED	Power Consumption	5.8 W
CE mark	CE mark	Power Factor (Fraction)	0.4
Warranty period	1 years	Connection	Screw connection block
Flammability mark	For mounting on normally flammable surfaces	Cable	Cable without plug 2-pole
Light Technical		Temperature	
Luminous Flux	250 lm	Ambient temperature range	-20 to +40 °C
Correlated Color Temperature (Nom)	4000 K	Controls and Dimming	
Luminous Efficacy (rated) (Nom)	43.10 lm/W	Dimmable	No
Color rendering index (CRI)	>70	Driver/power unit/transformer	Power supply unit (On/Off)
Number of light sources	96	Control interface	-
Light source color	740 neutral white	Number of products on MCB of 16 A type B 1	

LED Wall Mount

Constant light output	No
Mechanical and Housing	
Housing Material	Polycarbonate
Optical cover material	Polycarbonate
Housing Color	Dark gray
Mounting device	Allen screw fixation
Optical cover finish	Matte
Overall height	62 mm
Overall diameter	200 mm
Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%
Product Data	
Order product name	BWS150 LED200/NW PSU 220-240V 7043
Full product name	BWS150 LED200/NW PSU 220-240V 7043
Full product code	692382863161199
Order code	63161199
Material Nr. (12NC)	911401193880
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828631611
Numerator - Packs per outer box	24
EAN/UPC - Case	6923828631628

Dimensional drawing

